
# PARIS FLOW TECH

#### **YOUR BEST PARTNER IN CONTINUOUS FLOW CHEMISTRY**



PARIS FLOW TECH IS THE LEADING FRENCH TECHNOLOGY PLATFORM IN CONTINUOUS FLOW CHEMISTRY

#### **1<sup>ST</sup> APPLICATION QUALIFIED LAB (AQL) IN FRANCE**











#### **FLOW CHEMISTRY:** A REVOLUTION IN THE CHEMICAL INDUSTRY

SAFER REACTIONS

Inceased safety for hazardous reactions (exothermic, gas formation)

**INCREASED PRODUCT QUALITY** 

Better control over the reaction conditions

COSTS

Reduced maintenant costs and less waste products

MINIMIZED FLOOR AREA IN PRODUCTION PLANTS

Smaller volume of reactor necessary compared to batch

INTEGRATED SYNTHESIS

Allow for continuous work up and purification



#### **OUR EXPERTISE IN FLOW CHEMISTRY** WE SUPPORT YOU AT ALL LEVEL IN THE DEVELOPMENT OF YOUR FLOW CHEMISTRY

#### PROOF OF CONCEPT (POC)

Transposition batch to flow Innovative chemical activation (electro-, photo-, plasma chemistry) Optimization of reactions on Corning reactors



Up to several 100g per day on the platform CORNING Advanced-Flow systems allow for production up to tons/year

#### **ONLINE ANALYSIS & ANALYTICAL TOOLS**

In line GC analysis

Fully dedicated analytic park: GC-MS, LC-MS, NMR, Spectrocopy

#### AUTOMATED SYSTEMS

Innovative technology for screening (microlab) Home-made reactors






### **LOCATION** PARIS, FRANCE





#### **OUR EXPERTISE IN FLOW CHEMISTRY** A CONSORTIUM OF EXPERTS TO SUPPORT YOUR PROJECT



#### AVAILABLE TECHNOLOGIES ON THE PLATFORM

#### **COMMERCIAL REACTORS**



Révolutionnons l'industrie de la chimie

**HOME-MADE REACTORS** 

## **AVAILABLE TECHNOLOGIES**

#### FOR REACTION TESTING AND OPTIMISATION







- > 10 PLATES / 2 SKID
- ≻ -30°C TO 200°C
- POC ON RAPID REACTIONS WITH SHORT RESIDENCE TIMES (<MIN)</p>
  - > 1 PLATES G1
  - INTRODUCTION TO CORNING TECHNOLOGY FOR INDUSTRY AND STUDENT





- > 8 PLATES / 2 SKID
- ➤ -30°C TO 200°C
- > POC ON RAPID REACTIONS WITH RESIDENCE TIMES OF FEW MINS
- > OPTIMIZED PRODUCTION : 100G / HOUR
- > PHOTOCHEMICAL MODULE (8 X 20 LEDS λ=365, 385, 405, 470, 610, 4000K)


- > 2 PLATES
- ➤ -30°C TO 200°C
- > TESTING ON LARGER CHANNELS IF NECESSARY
- > FIRST SCALE UP FOR OPTIMIZED REACTION : KG / HOUR


CORNING

### **OUR TECHNOLOGIES ARE SCALABLE**



#### **INDUSTRIAL FLOW REACTORS AVAILABLE AT CORNING**





PRODUCTION

### **AVAILABLE TECHNOLOGIES**

#### **FOR PRESSURE & HEAT REACTIONS**





#### KHIMOD K1



- > LIQ ORGAS REACTIONS
- > HIGH PRESSURE (100 bars)
- ➢ HIGH TEMPERATURE (350°C)
- > VOLUME: 100 mL
- > FLOW: 10 L/min

#### AVAILABLE TECHNOLOGIES ON THE PLATFORM

#### **COMMERCIAL REACTORS**




Révolutionnons l'industrie de la chimie

**HOME-MADE REACTORS** 

#### **AVAILABLE TECHNOLOGIES** A UNIQUE ALL-IN-ONE MICROFLUIDIC PLATFORME AT IPGG

#### **HOME-MADE REACTORS – MICROFLUIDIC SYSTEMS**




### **AVAILABLE TECHNOLOGIES**

#### **HOME-MADE REACTORS – PHOTO, ELECTRO- AND PLASMA CHEMISTRY**

#### **PHOTOCHEMISTRY**



#### ELECTROCHEMISTRY



#### **PLASMA CHEMISTRY**





System versatility: wavelength, light intensity, different electrodes



Adaptability to different reactor size/shape




Energy and cost saving



Plasma chemistry: catalystfree, enable new reactions

### AVAILABLE TECHNOLOGIES ON THE PLATFORM

#### **HOME-MADE REACTORS - MICROLAB**



INSTITUT

DE GENNES

PIERRE-GILLES

PSL

#### **AN OFFER ADAPTED** TO INDUSTRIALISTS

> The presence of dedicated staff makes it easy to adapt to your needs



### **THE TEAM & CONTACTS**

Michael Tatoulian Coordinator

Mariane Ighilahriz Corporate Relations

Maxime Vitale Expert in photochemistry **Stéphanie Ognier** Expert in Flow Chemistry & Process Engineering

Janine Cossy Expert in molecular chemistry

**Benjamin Laroche** Expert in photochemistry Laurence Grimaud Expert en electrochemistry

**Paolo Stringari** Expert in process engineering, thermophysical properties





Email: julien.daubignard@chimieparistech.psl.eu Tel: +33 6 16 33 17 58

**JULIEN VINET** TEAM LEADER PARIS FLOW TECH

Email: julien.vinet@chimieparistech.psl.eu Tel: +33 6 75 98 34 19

bpifrance ¥

www.parisflowtech.fr



NSTITUT

PGG Microfluidique









